

VIP-PA-FLK50/FS/ 3,0M/S7 - Front adapter



2901463

<https://www.phoenixcontact.com/us/products/2901463>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP VARIOFACE front adapter, with connected system cables with 180° punched-on connector for SIMATIC S7-300, 1 x 32 channels can be connected, cable length: 3 m

Commercial data

Item number	2901463
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK232S
GTIN	4046356593878
Weight per piece (including packing)	766.001 g
Weight per piece (excluding packing)	766.001 g
Country of origin	DE

VIP-PA-FLK50/FS/ 3,0M/S7 - Front adapter



2901463

<https://www.phoenixcontact.com/us/products/2901463>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Dimensions

Cable

Length	3 m
--------	-----

Cable/line

50X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	50
Shielded	no
Cable type	50X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	50x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	10.30 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	86 mm
Smallest bending radius, movable installation	161 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-PA-FLK50/FS/ 3,0M/S7 - Front adapter

2901463

<https://www.phoenixcontact.com/us/products/2901463>



Classifications

ECLASS

ECLASS-13.0	27242292
-------------	----------

2901463

<https://www.phoenixcontact.com/us/products/2901463>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com