

CABLE-D25SUB/B/B/1020/KONFEK/S - Cable



2902260

<https://www.phoenixcontact.com/us/products/2902260>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled, shielded round cable, with two 25-pos. D-SUB female connectors (1:1 connection), cable length: 10.20 m

Commercial data

Item number	2902260
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	DK2AI2
GTIN	4046356652216
Weight per piece (including packing)	107.2 g
Weight per piece (excluding packing)	107.2 g
Country of origin	DE

CABLE-D25SUB/B/B/1020/KONFEK/S - Cable



2902260

<https://www.phoenixcontact.com/us/products/2902260>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 50 °C

Electrical properties

Operating voltage (AC)	≤ 25 V AC
Operating voltage (DC)	≤ 50 V DC
Current (Per path)	≤ 2 A (uncoiled)

Cable/line

Cable length	10.2 m
--------------	--------

25X0.25 [PVC]

UL AWM Style	2464/1061
Number of positions	25
Shielded	yes
Cable type	25X0.25 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross-section	25x 0.25 mm ²
Wire diameter incl. insulation	1.2 mm ±0.05 mm
External cable diameter	9.80 mm ±0.5 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	≤ 80 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (at 20 °C)
Smallest bending radius, fixed installation	82 mm
Smallest bending radius, movable installation	155 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1

CABLE-D25SUB/B/B/1020/KONFEK/S - Cable



2902260

<https://www.phoenixcontact.com/us/products/2902260>

Resistance to oil	can withstand occasional splashes (raw cable)
-------------------	---

Connection data

Field level

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	25
Conductor cross-section AWG	24

Controller level

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	25
Conductor cross-section AWG	24

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

CABLE-D25SUB/B/B/1020/KONFEK/S - Cable



2902260

<https://www.phoenixcontact.com/us/products/2902260>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com