

FUSE-10X38-30A-MR - Fuse



2903119

<https://www.phoenixcontact.com/us/products/2903119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 30 A, tripping characteristic: fast-blow (F)

Commercial data

Item number	2903119
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C470
Product key	DK7455
GTIN	4046356713320
Weight per piece (including packing)	8.53 g
Weight per piece (excluding packing)	8.53 g
Customs tariff number	85361050
Country of origin	MX

FUSE-10X38-30A-MR - Fuse



2903119

<https://www.phoenixcontact.com/us/products/2903119>

Technical data

Product properties

Product type	Fuse
Number of fuses in the set	10

Electrical properties

Tripping characteristic	fast-blow (F)
Nominal voltage U_N	690 V
Nominal current I_N	30 A
Fuse rating	CC
Fuse	Fuse

Dimensions

Dimensions	10 x 38 mm
------------	------------

FUSE-10X38-30A-MR - Fuse



2903119

<https://www.phoenixcontact.com/us/products/2903119>

Classifications

ECLASS

ECLASS-13.0

27142002

ETIM

ETIM 9.0

EC002704

UNSPSC

UNSPSC 21.0

39121600

FUSE-10X38-30A-MR - Fuse



2903119

<https://www.phoenixcontact.com/us/products/2903119>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com