

# MINI MCR-2-I-I-PT-SAMPLE - Sample



2905551

<https://www.phoenixcontact.com/us/products/2905551>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



NFC/mechanical sample of a MINI-MCR-2-I-I-PT 3-way signal conditioner with plug-in connection technology, no electrical function. push-in connection technology.

## Commercial data

Item number	2905551
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	NULL
Product key	DK112Z
GTIN	4046356962087
Weight per piece (including packing)	54.75 g
Weight per piece (excluding packing)	52.8 g
Customs tariff number	85437090
Country of origin	DE

## Technical data

### Product properties

Product type	Sample without function
--------------	-------------------------

### Connection data

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (with ferrule)
	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (without ferrule)
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12 (flexible)

### Dimensions

Width	6.2 mm
Height	109.81 mm
Depth	119.2 mm

### Material specifications

Color	gray (RAL 7042)
Housing material	PBT
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2

### Mounting

Mounting type	DIN rail mounting
Mounting position	any

# MINI MCR-2-I-I-PT-SAMPLE - Sample



2905551

<https://www.phoenixcontact.com/us/products/2905551>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905551>



**EAC**

Approval ID: RU C-DE.A\*30.B.01082

# MINI MCR-2-I-I-PT-SAMPLE - Sample



2905551

<https://www.phoenixcontact.com/us/products/2905551>

## Classifications

### ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

### ETIM

ETIM 9.0	EC002498
----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# MINI MCR-2-I-I-PT-SAMPLE - Sample



2905551

<https://www.phoenixcontact.com/us/products/2905551>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)