

# MACX MCR-EX-DUMMY-ISOLATOR-SP - Dummy



2905846

<https://www.phoenixcontact.com/us/products/2905846>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Dummy module with no function for connecting unused intrinsically safe signal cables, with plug-in push-in connection terminal blocks.

## Commercial data

Item number	2905846
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK121Z
GTIN	4046356999427
Weight per piece (including packing)	98.3 g
Weight per piece (excluding packing)	94.44 g
Country of origin	DE

## Technical data

### Product properties

Product type	Sample without function
--------------	-------------------------

### Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

### Dimensions

Width	17.5 mm
Height	116 mm
Depth	113.7 mm
Depth NS 35/7,5	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94 (Housing)	V0 (Housing)
Housing material	PA 6.6

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 80 °C
---	------------------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# MACX MCR-EX-DUMMY-ISOLATOR-SP - Dummy



2905846

<https://www.phoenixcontact.com/us/products/2905846>

## Classifications

### ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

### ETIM

ETIM 10.0	EC002886
-----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

2905846

<https://www.phoenixcontact.com/us/products/2905846>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)