

# UM 108-PROFIL 200CM - Profile

2906212

<https://www.phoenixcontact.com/us/products/2906212>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Drawn section panel mounting base, with a constructional width of 108 mm and a fixed length of 200 cm



The figure shows the variant UM 45-Profil CM

## Your advantages

- Easy installation
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts

## Commercial data

Item number	2906212
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918277420
Weight per piece (including packing)	1.1 kg
Weight per piece (excluding packing)	1.1 kg
Customs tariff number	39162000
Country of origin	DE

# UM 108-PROFIL 200CM - Profile

2906212


<https://www.phoenixcontact.com/us/products/2906212>

## Technical data

### Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Depth	21.5 mm
Length	200 cm

### External dimensions

Profile width (external)	107.5 mm
--------------------------	----------

### Internal dimensions

Profile width (internal)	122.6 mm
--------------------------	----------

### PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

### Material specifications

Color (Profile)	green (RAL 6021)
Material Profile	PVC

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 50 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Relative humidity (storage/transport)	95 %

### PCB data

Number of PCB holders	2
Thickness of the PCB	1.4 mm ... 1.8 mm

### Mounting

Mounting type	Latching with side elements, latching with foot element
---------------	---

# UM 108-PROFIL 200CM - Profile



2906212

<https://www.phoenixcontact.com/us/products/2906212>

Mounting position	parallel to the DIN rail
-------------------	--------------------------

## Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# UM 108-PROFIL 200CM - Profile




2906212

<https://www.phoenixcontact.com/us/products/2906212>

## Drawings

Dimensional drawing



# UM 108-PROFIL 200CM - Profile



2906212

<https://www.phoenixcontact.com/us/products/2906212>

## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM 108-PROFIL 200CM - Profile



2906212

<https://www.phoenixcontact.com/us/products/2906212>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)