

# UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting flange, for mounting directly on the wall



## Commercial data

Item number	2906380
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDCZ
GTIN	4017918277512
Weight per piece (including packing)	0.716 g
Weight per piece (excluding packing)	0.694 g
Customs tariff number	39269097
Country of origin	PL

# UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



## Technical data

### Product properties

Product type	Flange
Housing type	Press-drawn section housings
Housing series	UMK
Ventilation openings present	no

### Dimensions

Width	4.6 mm
Height	26 mm

### Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PA
Flammability rating according to UL 94	V2

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906380>



**UL Recognized**

Approval ID: E240868

# UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.009 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)