

UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting flange, for mounting directly on the wall



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2906380 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC13 |
| Product key | ACHDCZ |
| GTIN | 4017918277512 |
| Weight per piece (including packing) | 0.716 g |
| Weight per piece (excluding packing) | 0.694 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

UMK-BF BK - Mounting flange



2906380

<https://www.phoenixcontact.com/us/products/2906380>

Technical data

Product properties

| | |
|------------------------------|------------------------------|
| Product type | Flange |
| Housing type | Press-drawn section housings |
| Housing series | UMK |
| Ventilation openings present | no |

Dimensions

| | |
|--------|--------|
| Width | 4.6 mm |
| Height | 26 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V2 |
| Surface characteristics | untreated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906380>



UL Recognized

Approval ID: E240868

UMK-BF BK - Mounting flange

2906380

<https://www.phoenixcontact.com/us/products/2906380>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UMK-BF BK - Mounting flange



2906380

<https://www.phoenixcontact.com/us/products/2906380>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com