

UM 25/45-FEO 200 BK - Foot element



2906393

<https://www.phoenixcontact.com/us/products/2906393>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Foot element, is inserted in the profile housing, limit stop with screw. Mounted at right angles to the NS 35/7.5 DIN rail

Commercial data

Item number	2906393
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	NULL
Product key	ACHDBA
GTIN	4017918277529
Weight per piece (including packing)	6.532 g
Weight per piece (excluding packing)	6.29 g
Customs tariff number	39269097
Country of origin	PL

UM 25/45-FEO 200 BK - Foot element



2906393

<https://www.phoenixcontact.com/us/products/2906393>

Technical data

Product properties

Product type	Base latches
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM

Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PA
Flammability rating according to UL 94	V0

2906393

<https://www.phoenixcontact.com/us/products/2906393>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM 25/45-FEO 200 BK - Foot element



2906393

<https://www.phoenixcontact.com/us/products/2906393>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.041 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com