

UPS-BAT-KIT-VRLA 2X12V/12AH - Uninterruptible power supply replacement battery



2908235

<https://www.phoenixcontact.com/us/products/2908235>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Please use the following item for new systems: 1274119.
Replacement battery for UPS-BAT/VRLA... battery modules

Commercial data

Item number	2908235
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CM24
Product key	CMUEV3
GTIN	4055626297767
Weight per piece (including packing)	7,297 g
Weight per piece (excluding packing)	7,297 g
Customs tariff number	85072080
Country of origin	CN

UPS-BAT-KIT-VRLA 2X12V/12AH - Uninterruptible power supply replacement battery



2908235

<https://www.phoenixcontact.com/us/products/2908235>

Technical data

Input data

Input voltage	2x 12 V DC
---------------	------------

Energy storage

Nominal capacity	12 Ah
Battery module service life	6 Years ... 9 Years (20 °C)
Latest startup date (battery only)	12 Months (0 °C ... 20 °C)
Latest startup (battery only) - range	9 Months ... 12 Months (20 °C ... 30 °C)
	6 Months ... 9 Months (30 °C ... 40 °C)
Battery technology	VRLA-AGM
Accumulator type	Panasonic LC-VA1212PG1
IQ technology	no

Product properties

Product type	Battery
Product family	Replacement battery
IQ technology	no

Dimensions

Width	199 mm
Height	153 mm
Depth	100 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	≤ 95 %

UPS-BAT-KIT-VRLA 2X12V/12AH - Uninterruptible power supply replacement battery



2908235

<https://www.phoenixcontact.com/us/products/2908235>

Classifications

UNSPSC

UNSPSC 21.0	26111700
-------------	----------

UPS-BAT-KIT-VRLA 2X12V/12AH - Uninterruptible power supply replacement battery



2908235

<https://www.phoenixcontact.com/us/products/2908235>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

China RoHS

Environment friendly use period (EFUP)	EFUP-3 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com