FUSE 40A/32V ATOF - Fuse

2908357

https://www.phoenixcontact.com/us/products/2908357

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse, nominal current: 40 A, length: 19 mm, width: 5 mm, height: 18.8 mm

Commercial data

Item number	2908357
Packing unit	2 pc
Minimum order quantity	2 pc
Sales key	CM24
Product key	CMUEZ9
GTIN	4055626294766
Weight per piece (including packing)	2.55 g
Weight per piece (excluding packing)	2.4 g
Customs tariff number	85361050
Country of origin	CN

Technical data

Product properties

Product type	Fuse

Electrical properties

Tripping characteristic	C
Nominal current I_N	40 A
Fuse	Fuse (flat-type fuse for automotive applications)

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2908357

EAC
Approval ID: RU C-DE.BL08.B.00724

Classifications

ECLASS

ECLASS-13.0	27142008
ECLASS-15.0	27142008

ETIM

ETIM 10.0	EC002298

UNSPSC

UNSPSC 21.0	39121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com