

UPS-BAT-KIT-LI-ION 2X12V/120WH - Uninterruptible power supply replacement battery



2908370

<https://www.phoenixcontact.com/us/products/2908370>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-BAT/VRLA... battery modules



Commercial data

Item number	2908370
Packing unit	1 pc
Sales key	CM24
Product key	CMUEL3
GTIN	4055626297729
Weight per piece (including packing)	2,190 g
Weight per piece (excluding packing)	2,190 g
Customs tariff number	85076000
Country of origin	CN

UPS-BAT-KIT-LI-ION 2X12V/120WH - Uninterruptible power supply replacement battery



2908370

<https://www.phoenixcontact.com/us/products/2908370>

Technical data

Input data

Input voltage	2x 12 V DC
---------------	------------

Energy storage

Nominal capacity	120 Wh
Battery module service life	15 Years (20 °C)
Latest startup date (battery only)	24 Months (20 °C)
Battery technology	Lithium-Ion (LiFePO ₄)
Accumulator type	NEC ALM 12V7s HP
IQ technology	no

Product properties

Product type	Battery
Product family	Replacement battery
IQ technology	no

Dimensions

Width	129 mm
Height	151 mm
Depth	104 mm

Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	50 mm / 50 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 65 °C
Max. permissible relative humidity (operation)	≤ 80 %

UPS-BAT-KIT-LI-ION 2X12V/120WH - Uninterruptible power supply replacement battery



2908370

<https://www.phoenixcontact.com/us/products/2908370>

Classifications

UNSPSC

UNSPSC 21.0	26111700
-------------	----------

UPS-BAT-KIT-LI-ION 2X12V/120WH - Uninterruptible power supply replacement battery



2908370

<https://www.phoenixcontact.com/us/products/2908370>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com