

FA MCR-HT-D - Display

2908735

<https://www.phoenixcontact.com/us/products/2908735>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Display unit for plugging directly into the FA MCR-... head transmitter



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2908735 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C401 |
| Product key | DK114Z |
| GTIN | 4055626363097 |
| Weight per piece (including packing) | 37 g |
| Weight per piece (excluding packing) | 37 g |
| Customs tariff number | 85249100 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Digital displays |
|--------------|------------------|

Input data

Measurement

| | |
|------------|----------------|
| Resolution | 80 x 32 pixels |
|------------|----------------|

Connection data

| | |
|-------------------|---------------|
| Connection method | 4-pos. socket |
|-------------------|---------------|

Dimensions

| | |
|----------|---------|
| Depth | 29.7 mm |
| Diameter | 44 mm |

Material specifications

| | |
|-------|-----------------------|
| Color | light gray (RAL 7035) |
|-------|-----------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------------------|--------------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -30 °C ... 85 °C (-22 °F ... 185 °F) |
| Permissible humidity (operation) | non-condensing |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

FA MCR-HT-D - Display



2908735

<https://www.phoenixcontact.com/us/products/2908735>

Classifications

ECLASS

ECLASS-13.0

27210192

ETIM

ETIM 9.0

EC002498

UNSPSC

UNSPSC 21.0

39121000

2908735

<https://www.phoenixcontact.com/us/products/2908735>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com