

FA MCR-HT-D - Display

2908735

<https://www.phoenixcontact.com/us/products/2908735>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Display unit for plugging directly into the FA MCR-... head transmitter



Commercial data

Item number	2908735
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C401
Product key	DK114Z
GTIN	4055626363097
Weight per piece (including packing)	37 g
Weight per piece (excluding packing)	37 g
Customs tariff number	85249100
Country of origin	DE

FA MCR-HT-D - Display



2908735

<https://www.phoenixcontact.com/us/products/2908735>

Technical data

Product properties

Product type	Digital displays
--------------	------------------

Input data

Measurement

Resolution	80 x 32 pixels
------------	----------------

Connection data

Connection method	4-pos. socket
-------------------	---------------

Dimensions

Depth	29.7 mm
Diameter	44 mm

Material specifications

Color	light gray (RAL 7035)
-------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-30 °C ... 85 °C (-22 °F ... 185 °F)
Permissible humidity (operation)	non-condensing

Approvals

CE

Certificate	CE-compliant
-------------	--------------

FA MCR-HT-D - Display



2908735

<https://www.phoenixcontact.com/us/products/2908735>

Classifications

ECLASS

ECLASS-13.0

27210192

ETIM

ETIM 9.0

EC002498

UNSPSC

UNSPSC 21.0

39121000

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------