

# EG 67,5-G/ABS BEIGE - Mounting base housing



2909183

<https://www.phoenixcontact.com/us/products/2909183>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mounting base housing ,Component housing, length: 75 mm, Lower part, width: 67.5 mm, height: 107.5 mm

The figure shows a fully mounted version of the electronic housing

## Commercial data

Item number	2909183
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	ACHCGA
GTIN	4017918398606
Weight per piece (including packing)	59 g
Weight per piece (excluding packing)	8.35 g
Country of origin	PL

# EG 67,5-G/ABS BEIGE - Mounting base housing



2909183

<https://www.phoenixcontact.com/us/products/2909183>

## Technical data

### Product properties

Housing type	Component housing
Number of positions	26

### Dimensions

Width	67.5 mm
Installed height	107.5 mm
Height NS 35/7,5	107.5 mm
Depth	75 mm
Length	75 mm

### Material specifications

Flammability rating according to UL 94	HB
--	----

# EG 67,5-G/ABS BEIGE - Mounting base housing

2909183

<https://www.phoenixcontact.com/us/products/2909183>



## Classifications

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# EG 67,5-G/ABS BEIGE - Mounting base housing



2909183

<https://www.phoenixcontact.com/us/products/2909183>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)