

CAB-DSUB37F/RA/OE/22/TP/S/ 1M - Cable



2909708

<https://www.phoenixcontact.com/us/products/2909708>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled shielded round cable; connection 1: Twisted pair (37-position) (The wires are marked and fitted with ferrules); connection 2: D-SUB socket strip (1x 37-position); cable length: 1 m

Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Twisted-pair wires fitted with ferrules
- Screw connection: 2 UNC 4-40 screws
- Open end at one end
- D-SUB socket or pin strip at one end

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2909708 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK2BI4 |
| GTIN | 4055626682389 |
| Weight per piece (including packing) | 273 g |
| Weight per piece (excluding packing) | 260 g |
| Customs tariff number | 85444290 |
| Country of origin | US |

CAB-DSUB37F/RA/OE/22/TP/S/ 1M - Cable



2909708

<https://www.phoenixcontact.com/us/products/2909708>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Electrical properties

| | |
|------------------------|------------|
| Operating voltage (AC) | ≤ 125 V AC |
| Operating voltage (DC) | ≤ 125 V DC |
| Current (Per path) | ≤ 1 A |

Cable/line

| | |
|---------------------------------|--------------------------------|
| Cable length | 1 m |
| Shielded | yes |
| Conductor type | Assembled shielded round cable |
| Conductor structure signal line | 7x |
| AWG signal line | 22 |
| Conductor cross-section | 19x 0.36 mm ² |
| External cable diameter | 12.30 mm |
| Halogen-free | no |

Color code: Single-core wire

| | |
|--------|-------------------|
| black | D-SUB37 (1) = () |
| red | D-SUB37 (2) = () |
| black | D-SUB37 (3) = () |
| white | D-SUB37 (4) = () |
| black | D-SUB37 (5) = () |
| green | D-SUB37 (6) = () |
| black | D-SUB37 (7) = () |
| blue | D-SUB37 (8) = () |
| black | D-SUB37 (9) = () |
| yellow | D-SUB37 (10) = () |
| black | D-SUB37 (11) = () |
| brown | D-SUB37 (12) = () |
| black | D-SUB37 (13) = () |
| orange | D-SUB37 (14) = () |
| red | D-SUB37 (15) = () |
| white | D-SUB37 (16) = () |
| red | D-SUB37 (17) = () |

CAB-DSUB37F/RA/OE/22/TP/S/ 1M - Cable



2909708

<https://www.phoenixcontact.com/us/products/2909708>

| | |
|--------|-------------------|
| green | D-SUB37 (18) = () |
| red | D-SUB37 (19) = () |
| blue | D-SUB37 (20) = () |
| red | D-SUB37 (21) = () |
| yellow | D-SUB37 (22) = () |
| red | D-SUB37 (23) = () |
| brown | D-SUB37 (24) = () |
| red | D-SUB37 (25) = () |
| orange | D-SUB37 (26) = () |
| green | D-SUB37 (27) = () |
| white | D-SUB37 (28) = () |
| green | D-SUB37 (29) = () |
| blue | D-SUB37 (30) = () |
| green | D-SUB37 (31) = () |
| yellow | D-SUB37 (32) = () |
| green | D-SUB37 (33) = () |
| brown | D-SUB37 (34) = () |
| green | D-SUB37 (35) = () |
| orange | D-SUB37 (36) = () |
| white | D-SUB37 (37) = () |

Connection data

Field level

| | |
|-----------------------|--------------------|
| Connection method | D-SUB socket strip |
| Number of connections | 1 |
| Number of positions | 37 |

Controller level

| | |
|---------------------|---|
| Connection method | Twisted pair |
| Number of positions | 37 |
| Note | The wires are marked and fitted with ferrules |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

CAB-DSUB37F/RA/OE/22/TP/S/ 1M - Cable



2909708

<https://www.phoenixcontact.com/us/products/2909708>

Classifications

ECLASS

ECLASS-13.0

27242220

ETIM

ETIM 9.0

EC000237

UNSPSC

UNSPSC 21.0

26121600

CAB-DSUB37F/RA/OE/22/TP/S/ 1M - Cable



2909708

<https://www.phoenixcontact.com/us/products/2909708>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com