

VIP/S/MVSTBR/KIT CX - Connector set



2910416

<https://www.phoenixcontact.com/us/products/2910416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plug kit for use with VIP/MSTB/D50M/BASE..., screw connections



Your advantages

- Screw-clamp terminal wire connection
- Pre-printed channel labelling
- Pluggable for quick and easy connection to base module

Commercial data

Item number	2910416
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C480
Product key	DK115Z
GTIN	4055626478777
Weight per piece (including packing)	159.6 g
Weight per piece (excluding packing)	159.6 g
Customs tariff number	85366990
Country of origin	DE

VIP/S/MVSTBR/KIT CX - Connector set



2910416

<https://www.phoenixcontact.com/us/products/2910416>

Technical data

Product properties

Product type	PCB connector
Product family	VIP I/O-Marshalling

Electrical properties

Max. permissible current	10 A
Nominal voltage U_N	300 V (maximum continuous operating voltage)

Connection data

Field level

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	PA

VIP/S/MVSTBR/KIT CX - Connector set



2910416

<https://www.phoenixcontact.com/us/products/2910416>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------