

UM IA THERMOMARK ROLL - Manual



2910897

<https://www.phoenixcontact.com/us/products/2910897>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Manual, Ring manual for the THERMOMARK ROLL and THERMOMARK ROLL 2.0



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2910897 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | NULL |
| Product key | BG122Z |
| GTIN | 4046356647830 |
| Weight per piece (including packing) | 141.94 g |
| Weight per piece (excluding packing) | 148.2 g |
| Customs tariff number | 49019900 |
| Country of origin | DE |

UM IA THERMOMARK ROLL - Manual



2910897

<https://www.phoenixcontact.com/us/products/2910897>

Technical data

Product properties

Product type

Documentation

2910897

<https://www.phoenixcontact.com/us/products/2910897>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 25240908 |
| ECLASS-15.0 | 25240908 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 55111600 |
|-------------|----------|

2910897

<https://www.phoenixcontact.com/us/products/2910897>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com