

PLC-BSP- 24DC/21-21 - Relay base



2912439

<https://www.phoenixcontact.com/us/products/2912439>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



14 mm PLC basic terminal block with spring-cage connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 2 changeover contacts, input voltage 24 V DC

Commercial data

Item number	2912439
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C461
Product key	DK6222
GTIN	4046356050845
Weight per piece (including packing)	50.43 g
Weight per piece (excluding packing)	50.43 g
Customs tariff number	85369010
Country of origin	DE

PLC-BSP- 24DC/21-21 - Relay base



2912439

<https://www.phoenixcontact.com/us/products/2912439>

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---------------------------------------------------------------------------

Product properties

Product type	Relay socket
Product family	PLC-INTERFACE
Application	Universal
Set comprises	2912507 PLC-RSP- 24DC/21-21 2912578 PLC-RSP- 24DC/21-21AU
Operating mode	100% operating factor

Electrical properties

Protective circuit	Reverse polarity protection; Polarity protection diode
--------------------	--------------------------------------------------------

Input data

Nominal input voltage U_N	24 V DC
Protective circuit	Freewheeling diode
Nominal input voltage U_N	24 V DC

Connection data

Input side

Connection method	Spring-cage connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Output side

Connection method	Spring-cage connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Signaling

Status display	LED
----------------	-----

Dimensions

Width	14 mm
Height	80 mm

PLC-BSP- 24DC/21-21 - Relay base



2912439

<https://www.phoenixcontact.com/us/products/2912439>

Depth	94 mm
-------	-------

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94 (Housing)	V0 (Housing)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com