

WP 04T - Web panel



2913632

<https://www.phoenixcontact.com/us/products/2913632>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Web panel with 8.9 cm (3.5") graphics-capable TFT display, 320 x 240 pixels, 1x Ethernet, 2x USB, and integrated micro browser

Your advantages

- Energy efficient due to LED backlighting
- Easy device replacement - the visualization project is saved on the PLC (web server)
- Micro browser (WebVisit client) integrated as standard in all devices
- Display available in sizes from 8.9 cm (3.5") to 38.1 cm (15")
- Short startup time
- Easy installation, low installation depth, and compact design
- Low maintenance costs, as projects are only adapted once

Commercial data

Item number	2913632
Packing unit	1 pc
Sales key	DR17
Product key	DRCABD
GTIN	4046356460422
Weight per piece (including packing)	494.4 g
Weight per piece (excluding packing)	494.4 g
Customs tariff number	84714100
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	64 MB SDRAM
Data storage system	Flash, 32 MB

Display

Display type	8.9 cm / 3.5"-TFT
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	350 cd/m², typical (adjustable)
MTBF	40000 h
Color spectrum	65536 colors

Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	MicroBrowser
---------------	--------------

Electrical properties

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.3 A

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X

WP 04T - Web panel



2913632

<https://www.phoenixcontact.com/us/products/2913632>

Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Dimensions

Width	120 mm
Height	90 mm
Depth	40 mm

External dimensions

Width / Height / Depth	120 mm / 90 mm / 5 mm (Dimensions of the front plate)
------------------------	---

Installation dimensions

Width / Height / Installation depth	112 mm / 82 mm / 35 mm
-------------------------------------	------------------------

WP 04T - Web panel

2913632

<https://www.phoenixcontact.com/us/products/2913632>



Classifications

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	52d1b398-89b9-454b-ac5c-9c0fc5369ae6