

UM122-A/U92 L16,27CM SO5 - Covering hood



2914644

<https://www.phoenixcontact.com/us/products/2914644>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching, Cover, width: 92 mm, profile width (external): 92 mm, length: 162.7 mm, height: 34 mm, Note: max. length of the cover = PCB length - 19 mm



The figure shows a standard item

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2914644
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHDBZ
GTIN	4017918959579
Weight per piece (including packing)	72.15 g
Weight per piece (excluding packing)	56.95 g
Country of origin	DE

UM122-A/U92 L16,27CM SO5 - Covering hood



2914644

<https://www.phoenixcontact.com/us/products/2914644>

Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM122
Ventilation openings present	no

Dimensions

Width	92 mm
Height	34 mm
Length	162.7 mm

External dimensions

Profile width (external)	92 mm
--------------------------	-------

Material specifications

Color (Covering hood)	transparent
Material	PC
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	Latching
Mounting position	vertical or horizontal

UM122-A/U92 L16,27CM SO5 - Covering hood



2914644

<https://www.phoenixcontact.com/us/products/2914644>

Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM122-A/U92 L16,27CM SO5 - Covering hood



2914644

<https://www.phoenixcontact.com/us/products/2914644>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com