

UM 72-SEFE/R LBGY - Lateral element



2915863

<https://www.phoenixcontact.com/us/products/2915863>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, DIN rail mounting, Lateral element (right), with snap-on foot, width: 5 mm, height: 89.6 mm, depth: 37.6 mm



Your advantages

- Easy installation
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2915863 |
| Packing unit | 10 pc |
| Minimum order quantity | 250 pc |
| Note | Made to order (non-returnable) |
| Product key | ACHDBA |
| GTIN | 4046356177962 |
| Weight per piece (including packing) | 6.63 g |
| Weight per piece (excluding packing) | 6.59 g |
| Country of origin | PL |

UM 72-SEFE/R LBGY - Lateral element



2915863

<https://www.phoenixcontact.com/us/products/2915863>

Technical data

Product properties

| | |
|------------------------------|-------------------------------|
| Product type | Panel mounting base side part |
| Housing type | Press-drawn section housings |
| Housing series | UM |
| Product family | UM72 |
| Ventilation openings present | no |

Dimensions

| | |
|--------|---------|
| Width | 5 mm |
| Height | 89.6 mm |
| Depth | 37.6 mm |

Material specifications

| | |
|----------------------------------------|------------------|
| Color (Housing) | beige (RAL 7032) |
| Flammability rating according to UL 94 | V0 |
| Housing material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------|----------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

UM 72-SEFE/R LBGY - Lateral element



2915863

<https://www.phoenixcontact.com/us/products/2915863>

Classifications

ECLASS

ECLASS-13.0

27190602

ETIM

ETIM 9.0

EC002779

UNSPSC

UNSPSC 21.0

31261500

UM 72-SEFE/R LBGY - Lateral element



2915863

<https://www.phoenixcontact.com/us/products/2915863>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com