

# RAD-SYS-NEMA4X-900 - Control cabinet



2917188

<https://www.phoenixcontact.com/us/products/2917188>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

NEMA 4X enclosure for wireless systems



## Product description

NEMA 4X enclosure preconfigured for wireless systems. Includes UPS DC power supply, battery back-up, and surge protection for the antenna.

## Commercial data

Item number	2917188
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNC6P2
GTIN	4046356462082
Weight per piece (including packing)	6.943 g
Weight per piece (excluding packing)	8,330 g
Customs tariff number	85371091
Country of origin	US

# RAD-SYS-NEMA4X-900 - Control cabinet



2917188

<https://www.phoenixcontact.com/us/products/2917188>

## Set consists of

### MINI-DC-UPS/24DC/2 - Uninterruptible power supply

2866640

<https://www.phoenixcontact.com/us/products/2866640>



Uninterruptible power supply with integrated power supply unit, 2 A, in combination with MINI-BAT/24/DC 0.8 AH or 1.3 AH

---

### MINI-BAT/24DC/0.8AH - Battery module

2866666

<https://www.phoenixcontact.com/us/products/2866666>



Battery module (device with battery), lead AGM, VRLA technology, 24 V DC, 0.8 Ah.

# RAD-SYS-NEMA4X-900 - Control cabinet



2917188

<https://www.phoenixcontact.com/us/products/2917188>

## PLT-SEC-T3-230-P - Type 3 surge protection plug

2905235

<https://www.phoenixcontact.com/us/products/2905235>



Replacement plug for type 3 device protection from the PLUGTRAB SEC T3 product range. 230 V nominal voltage.

---

## CN-UB-70DC-6-BB - Surge protection device

2803166

<https://www.phoenixcontact.com/us/products/2803166>



Attachment plug with surge protection for coaxial signal interfaces. Connection: N connector, female/female

# RAD-SYS-NEMA4X-900 - Control cabinet



2917188

<https://www.phoenixcontact.com/us/products/2917188>

## Technical data

### Product properties

Product type	Control box
--------------	-------------

### Dimensions

Width	311 mm
Height	359 mm
Depth	156 mm

### Material specifications

Color	black
Housing material	Fiberglass

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	NEMA 4X
----------------------	---------

### Mounting

Mounting type	Panel mounting
---------------	----------------

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)