

EMG100-H 52MM GN - Covering hood



2944724

<https://www.phoenixcontact.com/us/products/2944724>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 100 mm

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2944724 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC11 |
| Product key | ACHCBA |
| GTIN | 4017918081676 |
| Weight per piece (including packing) | 44 g |
| Weight per piece (excluding packing) | 44 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

EMG100-H 52MM GN - Covering hood



2944724

<https://www.phoenixcontact.com/us/products/2944724>

Technical data

Product properties

| | |
|---------------------|--------------------|
| Product type | Upper housing part |
| Housing type | Component housing |
| Product family | EMG |
| Number of positions | 38 |

Dimensions

| | |
|------------------|--------|
| Width | 100 mm |
| Installed height | 52 mm |
| Depth | 75 mm |
| Length | 38 mm |

Material specifications

| | |
|--|-------------------------------------|
| Color | green |
| Flammability rating according to UL 94 | V0 |
| Housing material | Polycarbonate fiber reinforced PC-F |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

EMG100-H 52MM GN - Covering hood



2944724

<https://www.phoenixcontact.com/us/products/2944724>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com