

EMG 17-H 52MM GN - Covering hood



2946117

<https://www.phoenixcontact.com/us/products/2946117>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 17.5 mm

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2946117 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC11 |
| Product key | ACHCBA |
| GTIN | 4017918082079 |
| Weight per piece (including packing) | 11.05 g |
| Weight per piece (excluding packing) | 10.45 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

EMG 17-H 52MM GN - Covering hood



2946117

<https://www.phoenixcontact.com/us/products/2946117>

Technical data

Product properties

| | |
|---------------------|--------------------|
| Product type | Upper housing part |
| Housing type | Component housing |
| Product family | EMG |
| Number of positions | 6 |
| | 4 |

Dimensions

| | |
|------------------|---------|
| Width | 17.5 mm |
| Installed height | 52 mm |
| Depth | 75 mm |
| Length | 38 mm |

Material specifications

| | |
|----------------------------------------|-------------------------------------|
| Color | green |
| Flammability rating according to UL 94 | V0 |
| Housing material | Polycarbonate fiber reinforced PC-F |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

EMG 17-H 52MM GN - Covering hood



2946117

<https://www.phoenixcontact.com/us/products/2946117>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261501 |
|-------------|----------|

EMG 17-H 52MM GN - Covering hood



2946117

<https://www.phoenixcontact.com/us/products/2946117>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com