

# EMG 25-H 52MM GN - Covering hood

2947145

<https://www.phoenixcontact.com/us/products/2947145>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 25 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2947145       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AC11          |
| Product key                          | ACHCBA        |
| GTIN                                 | 4017918082611 |
| Weight per piece (including packing) | 13.44 g       |
| Weight per piece (excluding packing) | 13.32 g       |
| Customs tariff number                | 85472000      |
| Country of origin                    | DE            |

# EMG 25-H 52MM GN - Covering hood



2947145

<https://www.phoenixcontact.com/us/products/2947145>

## Technical data

### Product properties

|                              |                   |
|------------------------------|-------------------|
| Product type                 | Cover             |
| Housing type                 | Component housing |
| Housing series               | EMG               |
| Product family               | EMG               |
| Number of positions          | 8                 |
| Ventilation openings present | no                |

### Dimensions

|        |       |
|--------|-------|
| Width  | 25 mm |
| Depth  | 75 mm |
| Length | 38 mm |

### Material specifications

|  |                             |
|--|-----------------------------|
| Color (Housing)                        | green (RAL 6021)            |
| Material Housing                       | PC (glass-fiber reinforced) |
| Flammability rating according to UL 94 | V0                          |

### Mounting

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

# EMG 25-H 52MM GN - Covering hood



2947145

<https://www.phoenixcontact.com/us/products/2947145>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190603 |
| ECLASS-15.0 | 27190603 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# EMG 25-H 52MM GN - Covering hood



2947145

<https://www.phoenixcontact.com/us/products/2947145>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.031 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)