

EMG 25-LG - Electronics housing



2948319

<https://www.phoenixcontact.com/us/products/2948319>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, with snap foot for DIN rail EN 50022 for PCB insertion, without screw connection terminal blocks and cover

Commercial data

Item number	2948319
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCBA
GTIN	4017918083267
Weight per piece (including packing)	30.6 g
Weight per piece (excluding packing)	29.57 g
Customs tariff number	84879090
Country of origin	DE

EMG 25-LG - Electronics housing

2948319

<https://www.phoenixcontact.com/us/products/2948319>




Technical data

Product properties

Product type	Complete housing
Housing type	Component housing
Housing type	Basic housing
Housing series	EMG
Product family	EMG
Type	Lower part of housing, removable cover optional
Number of positions	8
Pitch	5 mm
Ventilation openings present	no

Dimensions

Dimensional drawing	
Width	25 mm
Installed height	47.5 mm
Height NS 35/7,5	55 mm
	100 mm
Depth	75 mm
Length	75 mm
Pitch	5 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PC (glass-fiber reinforced)
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Drawings

Dimensional drawing



Pitch 5 mm

a = Area for mounting components, 38 mm in the hood

b = Area for mounting components, 45 mm in the housing


EMG 25-LG - Electronics housing

2948319

<https://www.phoenixcontact.com/us/products/2948319>



Dimensional drawing



1 = Top edge of the PCB

B = Housing width

EMG 25-LG - Electronics housing

2948319

<https://www.phoenixcontact.com/us/products/2948319>



Classifications

ECLASS

ECLASS-13.0	27190101
ECLASS-15.0	27190101

ETIM

ETIM 10.0	EC001031
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG 25-LG - Electronics housing



2948319

<https://www.phoenixcontact.com/us/products/2948319>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.306 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com