# UM-BEFE 35 - Base element

2955564

https://www.phoenixcontact.com/us/products/2955564

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element with snap-on foot, for mounting on NS 32 or NS 35/7.5 DIN rail, with ribs, L = 35 mm



The figure shows a combination of versions UM-SE, UM 16,5 BE, UM-BE 35, UM-BEFE 35, UM-SE-A 73 and UM-A/U 73 CM

## Commercial data


| | |
|---|---|
| Item number | 2955564 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC13 |
| Product key | ACHDDA |
| GTIN | 4017918085537 |
| Weight per piece (including packing) | 21.23 g |
| Weight per piece (excluding packing) | 21.18 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Component housing lower part |
| Housing type | Press-drawn section housings |
| Housing type | Plug-in module DIN rail-mount base |
| Housing series | UM |
| Product family | UM BE |
| Ventilation openings present | no |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  1 - 3 |
| Width | 35 mm |
| Height | 111 mm |
| Depth | 27.7 mm |

### Material specifications

| | |
|---|---|
| Color (Housing) | green (RAL 6021) |
| Material | PA |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

### PCB data


| | |
|---|---|
| Number of PCB holders | 1 |

### Mounting


| | |
|---|---|
| Mounting type | DIN rail mounting |

## Drawings

Dimensional drawing



Dimensional drawing



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2955564

**UL Recognized**
Approval ID: E240868

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190601 |
| ECLASS-15.0 | 27190601 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002779 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.349 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com