

UM-BE 35 GY - Base element

2958778

<https://www.phoenixcontact.com/us/products/2958778>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, DIN rail mounting, Plug-in module base element, with ribs, without snap-on foot



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2958778 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | ACHDDA |
| GTIN | 4017918279912 |
| Weight per piece (including packing) | 20 g |
| Weight per piece (excluding packing) | 20 g |
| Country of origin | PL |

UM-BE 35 GY - Base element



2958778

<https://www.phoenixcontact.com/us/products/2958778>

Technical data

Product properties

| | |
|------------------------------|------------------------------------|
| Product type | Component housing lower part |
| Housing type | Press-drawn section housings |
| Housing type | Plug-in module DIN rail-mount base |
| Housing series | UM |
| Product family | UM BE |
| Ventilation openings present | no |

Material specifications

| | |
|-----------------|-----------------|
| Color (Housing) | gray (RAL 7042) |
| Material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

PCB data

| | |
|-----------------------|---|
| Number of PCB holders | 1 |
|-----------------------|---|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

UM-BE 35 GY - Base element



2958778

<https://www.phoenixcontact.com/us/products/2958778>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2958778>



UL Recognized

Approval ID: E240868

UM-BE 35 GY - Base element



2958778

<https://www.phoenixcontact.com/us/products/2958778>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190601 |
| ECLASS-15.0 | 27190601 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-BE 35 GY - Base element



2958778

<https://www.phoenixcontact.com/us/products/2958778>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.136 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com