SD-F/SC/LA - Socket

2963336

https://www.phoenixcontact.com/us/products/2963336

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Socket, color: green, standards/specifications: IEC 83, DIN 49440-1

Commercial data

Item number	2963336
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE76
Product key	BE7612
GTIN	4017918190699
Weight per piece (including packing)	80.87 g
Weight per piece (excluding packing)	80.87 g
Customs tariff number	85366990
Country of origin	GR

Technical data

Product properties

Product type	Socket
For country-specific use in	F

Signaling

Status display	Glow lamp or LED with preresistor

Dimensions

Width	45 mm
Height	75 mm
Depth	70.5 mm

Material specifications

Color	green
Insulating material	PA
Contact material	CuZn38

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C


Standards and regulations

Standards

Standards/regulations	IEC 83
	DIN 49440-1

Drawings

Circuit diagram



Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com