

SD-D/SP/YE - Socket



2963462

<https://www.phoenixcontact.com/us/products/2963462>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Socket, color: yellow, standards/specifications: IEC 83, DIN 49440-1



Commercial data

Item number	2963462
Packing unit	5 pc
Minimum order quantity	1 pc
Product key	BE7621
GTIN	4017918590529
Weight per piece (including packing)	74.6 g
Weight per piece (excluding packing)	58.844 g
Country of origin	GR

SD-D/SP/YE - Socket



2963462

<https://www.phoenixcontact.com/us/products/2963462>

Technical data

Product properties

Product type	Socket
For country-specific use in	D

Signaling

Status display	no
----------------	----

Dimensions

Width	45 mm
Height	75 mm
Depth	65.2 mm

Material specifications

Color	yellow
Insulating material	PA
Contact material	CuZn38

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C

Standards and regulations

Standards

Standards/regulations	IEC 83
	DIN 49440-1

SD-D/SP/YE - Socket

2963462

<https://www.phoenixcontact.com/us/products/2963462>



Drawings

Circuit diagram



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------