

UM 45-FLKS60/ZFKDS - Termination board



2968441

<https://www.phoenixcontact.com/us/products/2968441>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with three-level spring-cage connection and flat-ribbon cable connector, for mounting on NS 35/7.5, 60-pos.

The figure shows a 40-position version

Commercial data

Item number	2968441
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK21A1
GTIN	4017918932794
Weight per piece (including packing)	183.4 g
Weight per piece (excluding packing)	175.27 g
Customs tariff number	85369010
Country of origin	DE

UM 45-FLKS60/ZFKDS - Termination board



2968441

<https://www.phoenixcontact.com/us/products/2968441>

Technical data

Product properties

Product type	Interface module
Number of positions	60

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Spring-cage connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 14

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	60
Pitch	2.54 mm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	126 mm
Height	45 mm
Depth	61 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

UM 45-FLKS60/ZFKDS - Termination board



2968441

<https://www.phoenixcontact.com/us/products/2968441>

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM 45-FLKS60/ZFKDS - Termination board



2968441

<https://www.phoenixcontact.com/us/products/2968441>

Drawings

Circuit diagram



UM 45-FLKS60/ZFKDS - Termination board



2968441

<https://www.phoenixcontact.com/us/products/2968441>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com