

UMK- 8 RELS/KSR-24/21/21 - Multiple relay module



2975722

<https://www.phoenixcontact.com/us/products/2975722>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with plug-in bases for 8 miniature relays with 2 changeover contacts, with LED display

Commercial data

Item number	2975722
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK616Y
GTIN	4017918100810
Weight per piece (including packing)	263.3 g
Weight per piece (excluding packing)	255.9 g
Customs tariff number	85364190
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Multi-channel relay module
No. of channels	8
Compatible components	Miniature relays or miniature optocouplers
With components	no

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Input data

Nominal input voltage U_N	24 V DC \pm 10 %
Input voltage range in reference to U_N	0.9 ... 1.1
Protective circuit	Freewheeling diode; Freewheeling diode Reverse polarity protection; Polarity protection diode
Status display/channel	Yellow LED

Output data

Compatible components	Miniature relays or miniature optocouplers
-----------------------	--

Switching

Contact switching type	2 changeover contacts
Maximum switching voltage	250 V AC
Limiting continuous current	5 A
Error detection (line break / short-circuit)	no

Connection data

Input

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Number of connections	1
Number of positions	10
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 14

UMK- 8 RELS/KSR-24/21/21 - Multiple relay module



2975722

<https://www.phoenixcontact.com/us/products/2975722>

Output

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Number of connections	48
Number of positions	6
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 14

Signaling

Status display present	yes
------------------------	-----

Dimensions

Width	168.8 mm
Height	77 mm
Depth	59 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC, side panel PA non-reinforced,

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN VDE 0110
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

UMK- 8 RELS/KSR-24/21/21 - Multiple relay module



2975722

<https://www.phoenixcontact.com/us/products/2975722>

Classifications

UNSPSC

UNSPSC 21.0	39122335
-------------	----------

2975722

<https://www.phoenixcontact.com/us/products/2975722>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com