

UMK-BF - Mounting flange

2976077

<https://www.phoenixcontact.com/us/products/2976077>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting flange, for mounting directly on the wall



Commercial data

Item number	2976077
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC13
Product key	ACHDCZ
GTIN	4017918089207
Weight per piece (including packing)	0.7 g
Weight per piece (excluding packing)	0.6 g
Customs tariff number	39269097
Country of origin	DE

UMK-BF - Mounting flange

2976077

<https://www.phoenixcontact.com/us/products/2976077>



Technical data

Product properties

Product type	Flange
Housing type	Press-drawn section housings
Housing series	UMK
Ventilation openings present	no

Dimensions

Width	4.6 mm
Height	26 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

UMK-BF - Mounting flange

2976077

<https://www.phoenixcontact.com/us/products/2976077>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2976077>



UL Recognized

Approval ID: E240868

UMK-BF - Mounting flange

2976077

<https://www.phoenixcontact.com/us/products/2976077>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UMK-BF - Mounting flange

2976077

<https://www.phoenixcontact.com/us/products/2976077>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.009 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com