
PLC-BP (A1-14/A2-13) - Single plug-in bridge

2980296

https://www.phoenixcontact.com/us/products/2980296

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Passive feed-through bridge; can be inserted instead of a relay or solid-state relay, bridges terminal points (A1 and 14) and (A2 and 13)

Commercial data

Item number	2980296
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C461
Product key	DK62Z5
GTIN	4017918882174
Weight per piece (including packing)	4.86 g
Weight per piece (excluding packing)	4.86 g
Customs tariff number	85389099
Country of origin	HU

Technical data

Product properties

Product type	Bridge
Product family	PLC-INTERFACE

Approvals

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

Classifications

ECLASS

ECLASS-13.0	27371692
ECLASS-15.0	27371692

ETIM

ETIM 10.0	EC002586

UNSPSC

UNSPSC 21.0	39122300

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com