

PLC-SP-S/H - Switch

2980746

<https://www.phoenixcontact.com/us/products/2980746>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-RELAY with integrated switch (actuation: Manual) with spring-cage connection, for mounting on DIN rail NS 35/7.5, input voltage ≤ 72 V DC

The figure shows a version with a screw connection

Your advantages

- Just 6.2 mm wide
- Floating confirmation contact
- Screw- and Push-in connection

Commercial data

Item number	2980746
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C461
Product key	DK622H
GTIN	4046356051484
Weight per piece (including packing)	28.28 g
Weight per piece (excluding packing)	25.935 g
Customs tariff number	85364900
Country of origin	DE

PLC-SP-S/H - Switch

2980746

<https://www.phoenixcontact.com/us/products/2980746>



Technical data

Product properties

Product type	Switch module
Product family	PLC-INTERFACE
Operating mode	100% operating factor

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Rated insulation voltage	85 V AC
Rated surge voltage	0.5 kV

Output data

Switching

Maximum switching voltage	72 V DC
Minimum switching voltage	2 V DC
Maximum inrush current	50 mA
Min. switching current	1 mA
Switching cycles, max.	100 (At 72 V DC / 50 mA) 10000 (at 12 V DC / 100 mA)
Insulation resistance	100 MΩ

Connection data

Input side

Connection method	Spring-cage connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Output side

Connection method	Spring-cage connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

PLC-SP-S/H - Switch



2980746

<https://www.phoenixcontact.com/us/products/2980746>

Dimensions

Width	6.2 mm
Height	80 mm
Depth	90 mm

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94 (Housing)	V0 (Housing)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

PLC-SP-S/H - Switch


2980746

<https://www.phoenixcontact.com/us/products/2980746>



Drawings

Application drawing




PLC-SP-S/H - Switch

2980746

<https://www.phoenixcontact.com/us/products/2980746>




Application drawing



PLC-SP-S/H - Switch

2980746

<https://www.phoenixcontact.com/us/products/2980746>



PLC-SP-S/H - Switch



2980746

<https://www.phoenixcontact.com/us/products/2980746>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com