

CABLE-15/8/250/RSM/INDRADYN-2 - Adapter cable



2986986

<https://www.phoenixcontact.com/us/products/2986986>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable adapter for PSR over-speed safety relays (PSR-RSM4 and PSR-MM30), cable length: 2.5 m, for controller: Bosch Rexroth Indramat, type: IndraDrive - IndraDyn



The figure shows a version for Siemens, Heidenhain control system

Your advantages

- Option to connect to safe PSR-RSM4 and PSR-MM30 over-speed safety relays
- Suitable for connection to the existing motor feedback interface of an electrical drive
- Controller type: REXROTH
- 15-pos. D-SUB connection
- Length of connecting cable to over-speed safety relay: 2.5 m

Commercial data

Item number	2986986
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNA251
GTIN	4046356477222
Weight per piece (including packing)	168.9 g
Weight per piece (excluding packing)	167.9 g
Country of origin	DE

CABLE-15/8/250/RSM/INDRADYN-2 - Adapter cable



2986986

<https://www.phoenixcontact.com/us/products/2986986>

Technical data

Product properties

Product type	Adapter cable
--------------	---------------

Connection data

To the device

Connection method	RJ45
-------------------	------

Encoder / PLC

Connection method	D-SUB-15 male/D-SUB-15 female
Number of positions	15

Material specifications

Outer sheath, material	LSHF (FRNC)
Conductor material	Bare Cu litz wires

Cable/line

Cable length	2.5 m
Outer sheath, material	LSHF (FRNC)
Cable cross section	0.48 mm ² (AWG 26)
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield Soldering on D-SUB housing
Cable resistance	≤ 260 Ω/km

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation)
	0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

CABLE-15/8/250/RSM/INDRADYN-2 - Adapter cable



2986986

<https://www.phoenixcontact.com/us/products/2986986>

Classifications

ECLASS

ECLASS-13.0

27371390

ETIM

ETIM 9.0

EC002498

UNSPSC

UNSPSC 21.0

26121600

CABLE-15/8/250/RSM/INDRADYN-2 - Adapter cable



2986986

<https://www.phoenixcontact.com/us/products/2986986>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com