VISU+ 2 RT UNLIMITED WEB1 AD - Visualization software

2988104

https://www.phoenixcontact.com/us/products/2988104

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Runtime license for Visu+ including alarm dispatcher function and 1 web client where the I/O data and variables in scripting are not limited.

Your advantages

- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Control coupling with OPC

Commercial data

Item number	2988104
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR13
Product key	DRDAAB
GTIN	4046356525916
Weight per piece (including packing)	22 g
Weight per piece (excluding packing)	20 g
Customs tariff number	49119900
Country of origin	DE

Technical data

Product properties

Product type	Visualization

System properties

Intended use for the software	Visualization

License information

Type of license	Runtime license

Functionality

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Advanced alarm management with SMS, FAX, e-mail and voice mail function
Integrated function	Online configuration
	Password protection
	Language selection
	Alarm management
	Web client
Number of I/O nodes	128000
Number of clients	1

System requirements

Processor	Intel® Celeron® / Pentium® 1.6 GHz
Hard disk memory	min. 1 GByte (recommended: 2 GB)
Main memory (RAM)	min. 1 GByte (2 GB for Windows Vista and Windows 7)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Screen resolution	1024 x 768 pixel(s) (XGA)

System requirements for development environment

Operating equipment	Keyboard, mouse
Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2

	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003

System requirements for runtime environment

Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® XP Embedded
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003
	Windows® CE 5.0
	Windows® CE 6.0
	Windows® Mobile

Classifications

ECLASS

ECLASS-13.0	27242502

ETIM

ETIM 9.0	EC001416

UNSPSC

UNSPSC 21.0	43231500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com