

# PC WORX PRO LIC CPY - Programming software



2988560

<https://www.phoenixcontact.com/us/products/2988560>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The PC WORX PRO copy license enables the installation and parallel use of the PC WORX PRO software on multiple workstations. It is a workstation license. A workstation full license is also required.

## Commercial data

Item number	2988560
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR13
Product key	DRDBAC
GTIN	4046356305365
Weight per piece (including packing)	22 g
Weight per piece (excluding packing)	20 g
Customs tariff number	49119900
Country of origin	DE

## Technical data

### Product properties

Product type	Programming
--------------	-------------

### System properties

Control system	(Target system) Embedded and PC-based controllers
Type of software	On-premises
Intended use for the software	Engineering software for controllers

### License information

Type of license	Single-user license
	Freeware
	Copying license

### Functionality

Basic functions	Planning an automation system, parameterizing the INTERBUS and PROFINET devices, operating INTERBUS and PROFINET, programming an automation system in acc. with IEC 61131-3. communication in acc. with IEC 61131-5
	Network configuration (functionality of Config+)
	Network diagnostics (functionality of Diag+)
Expanded functionality	Unlimited number of input/output data
	Machine Sequential Function Chart (MSFC)
	Fixed Format Ladder Editor (FFLD)
Integrated function	Analysis
	Evaluation
	Data acquisition
	Programming
	Configuration
	Diagnostics
	Maintenance
	Communication
Programming languages supported	Functional safety
	Instruction list (IL)
	Function block diagram (FBD)
	Ladder diagram (LD)
	Structured text (ST)
	Symbolic flowchart (SFC)
	Fixed Format Ladder Editor (FFLD)
	Machine sequential function chart (MSFC)
Configuration	INTERBUS
	PROFINET
	Modbus/TCP
Diagnostics	INTERBUS

# PC WORX PRO LIC CPY - Programming software



2988560

<https://www.phoenixcontact.com/us/products/2988560>

	PROFINET
Control system	(Target system) Embedded and PC-based controllers
Associated hardware	Phoenix Contact control
Number of I/O nodes	128000

## System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (32-bit/64-bit), as of Build 1511
	Windows®11, as of Build 22000.675
Processor	min. 2 GHz, x86 architecture
Hard disk memory	min. 2 GByte
Interfaces	Serial COM port, Ethernet (PCI if there is an INTERBUS master card in the PC)
Supported browsers	Internet Explorer Version 8 or later
Languages supported	German, English, French, Italian, Spanish, Chinese
Screen resolution	SXGA (1280 x 1024)

2988560

<https://www.phoenixcontact.com/us/products/2988560>

## Classifications

### ECLASS

ECLASS-13.0

27242501

### ETIM

ETIM 9.0

EC000809

### UNSPSC

UNSPSC 21.0

43233600

2988560

<https://www.phoenixcontact.com/us/products/2988560>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)