

# VISU+ 2 RT 256 - Visualization software



2988609

<https://www.phoenixcontact.com/us/products/2988609>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Runtime license for Visu+ where the I/O data and variables in scripting are limited to 256 bytes.



## Your advantages

- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Control coupling with OPC

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2988609                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | DR13                           |
| Product key                          | DRDAAB                         |
| GTIN                                 | 4046356479691                  |
| Weight per piece (including packing) | 30.2 g                         |
| Weight per piece (excluding packing) | 20 g                           |
| Customs tariff number                | 49119900                       |
| Country of origin                    | DE                             |

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Visualization |
|--------------|---------------|

### System properties

|                               |               |
|-------------------------------|---------------|
| Intended use for the software | Visualization |
|-------------------------------|---------------|

### License information

|                 |                 |
|-----------------|-----------------|
| Type of license | Runtime license |
|-----------------|-----------------|

### Functionality

|                     |  |
|---------------------|--|
| Basic functions     | Know-How protection and safety through encoding of projects                |
|                     | Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server |
|                     | FDA CFR 21 Part 11 compatible  |
| Integrated function | Online configuration   |
|                     | Password protection  |
|                     | Language selection   |
| Number of I/O nodes | 256  |

### System requirements

|                     |                                  |
|---------------------|----------------------------------|
| Hard disk memory    | min. 1 GByte (recommended: 2 GB) |
| Supported browsers  | Internet Explorer 5.5 or higher  |
| Languages supported | German, English, French, Italian |
| Screen resolution   | 1024 x 768 pixel(s) (XGA)        |

### System requirements for development environment

|                      |                              |
|----------------------|------------------------------|
| Operating equipment  | Keyboard, mouse              |
| Operating system     | Windows® 11                  |
|                      | Windows® 10                  |
|                      | Windows® 8.1                 |
|                      | Windows® 8                   |
|                      | Windows® 7                   |
|                      | Windows® Embedded Standard 7 |
|                      | Windows® Server 2019         |
|                      | Windows® Server 2016         |
|                      | Windows® Server 2012 R2      |
|                      | Windows® Server 2012         |
|                      | Windows® Server 2008 R2      |
| Windows® Server 2008 |                              |
| Windows® Server 2003 |                              |

### System requirements for runtime environment

|                  |             |
|------------------|-------------|
| Operating system | Windows® 11 |
|                  | Windows® 10 |

# VISU+ 2 RT 256 - Visualization software



2988609

<https://www.phoenixcontact.com/us/products/2988609>

|  |                              |
|--|------------------------------|
|  | Windows® 8.1                 |
|  | Windows® 8                   |
|  | Windows® 7                   |
|  | Windows® Embedded Standard 7 |
|  | Windows® XP Embedded         |
|  | Windows® Server 2019         |
|  | Windows® Server 2016         |
|  | Windows® Server 2012 R2      |
|  | Windows® Server 2012         |
|  | Windows® Server 2008 R2      |
|  | Windows® Server 2008         |
|  | Windows® Server 2003         |
|  | Windows® CE 5.0              |
|  | Windows® CE 6.0              |
|  | Windows® Mobile              |

2988609

<https://www.phoenixcontact.com/us/products/2988609>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242502 |
| ECLASS-15.0 | 27242502 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001416 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43231500 |
|-------------|----------|

2988609

<https://www.phoenixcontact.com/us/products/2988609>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.039 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)