

IB EMULATOR - Simulation hardware



2988638

<https://www.phoenixcontact.com/us/products/2988638>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



With the IB emulator (and WINMOD from Mewes&Partner, www.winmod.de) it is possible to simulate 112 INTERBUS devices and the program test without a real system. No hardware is required for the simulation of PROFINET devices.

Commercial data

Item number	2988638
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	NULL
Product key	DRECAA
GTIN	4046356306799
Weight per piece (including packing)	964.1 g
Weight per piece (excluding packing)	964.1 g
Customs tariff number	85389091
Country of origin	DE

2988638

<https://www.phoenixcontact.com/us/products/2988638>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Simulator card
--------------	----------------

System properties

INTERBUS-Master

Amount of process data (Local bus)	max. 4096 Byte (INTERBUS-Master)
Number of supported devices	max. 112 (of which 112 are remote bus devices)

Electrical properties

Potentials

Power consumption	6.25 W
-------------------	--------

Input data

Digital:

Number of inputs	4096
------------------	------

Output data

Digital:

Number of outputs	4096
-------------------	------

Connection data

INTERBUS

Connection method	9-pos. D-SUB plug/socket
-------------------	--------------------------

Dimensions

Width	75 mm
Height	185 mm
Depth	190 mm

2988638

<https://www.phoenixcontact.com/us/products/2988638>

Classifications

ECLASS

ECLASS-13.0

27242211

ETIM

ETIM 9.0

EC000238

UNSPSC

UNSPSC 21.0

32151700

2988638

<https://www.phoenixcontact.com/us/products/2988638>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com