

CF FLASH 256MB - Memory



2988780

<https://www.phoenixcontact.com/us/products/2988780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Program and configuration memory, plug-in, 256 MB



Product description

Program and configuration memory to save the application programs and other files in the file system of the PLC. Alternatively, a program and configuration memory with integrated license is available to disconnect various function blocks.

Commercial data

Item number	2988780
Packing unit	1 pc
Sales key	DR10
Product key	DRAAZA
GTIN	4046356184984
Weight per piece (including packing)	16.5 g
Weight per piece (excluding packing)	15 g
Customs tariff number	85235110
Country of origin	TW

CF FLASH 256MB - Memory

2988780

<https://www.phoenixcontact.com/us/products/2988780>



Technical data

Product properties

Product type	Storage medium
Application	Program/configuration memory
Memory type	FLASH-EPROM
Memory size	256 Mbyte

Electrical properties

Maximum power dissipation for nominal condition	0.4 W
---	-------

Supply

Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC
Typical current consumption	typ. 120 mA

Dimensions

Width	36.4 mm
Height	42.8 mm
Depth	3.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

CF FLASH 256MB - Memory

2988780

<https://www.phoenixcontact.com/us/products/2988780>



Classifications

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

CF FLASH 256MB - Memory



2988780

<https://www.phoenixcontact.com/us/products/2988780>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com