

CF FLASH 256MB - Memory



2988780

<https://www.phoenixcontact.com/us/products/2988780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Program and configuration memory, plug-in, 256 MB



Product description

Program and configuration memory to save the application programs and other files in the file system of the PLC. Alternatively, a program and configuration memory with integrated license is available to disconnect various function blocks.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2988780 |
| Packing unit | 1 pc |
| Sales key | DR10 |
| Product key | DRAAZA |
| GTIN | 4046356184984 |
| Weight per piece (including packing) | 16.5 g |
| Weight per piece (excluding packing) | 15 g |
| Customs tariff number | 85235110 |
| Country of origin | TW |

CF FLASH 256MB - Memory

2988780

<https://www.phoenixcontact.com/us/products/2988780>



Technical data

Product properties

| | |
|--------------|------------------------------|
| Product type | Storage medium |
| Application | Program/configuration memory |
| Memory type | FLASH-EPROM |
| Memory size | 256 Mbyte |

Electrical properties

| | |
|---|-------|
| Maximum power dissipation for nominal condition | 0.4 W |
|---|-------|

Supply

| | |
|-----------------------------|---------------------------|
| Supply voltage | 3.3 V DC |
| Supply voltage range | 3.135 V DC ... 3.465 V DC |
| Typical current consumption | typ. 120 mA |

Dimensions

| | |
|--------|---------|
| Width | 36.4 mm |
| Height | 42.8 mm |
| Depth | 3.3 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
|---------------------------------|------------------|

CF FLASH 256MB - Memory

2988780

<https://www.phoenixcontact.com/us/products/2988780>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32101600 |
|-------------|----------|

CF FLASH 256MB - Memory



2988780

<https://www.phoenixcontact.com/us/products/2988780>

Environmental product compliance

EU RoHS

| | |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com