

CF FLASH 256MB APPLIC A - Memory



2988793

<https://www.phoenixcontact.com/us/products/2988793>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 256 MB with license key for function block libraries. For licensed function blocks, please refer to the documentation.

Your advantages

- License key for the function block libraries
- For storing application programs and other files in the file system of the PLC
- Program and configuration memory, plug-in, with license key for function block libraries

Commercial data

Item number	2988793
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR10
Product key	DRAAZA
GTIN	4046356332590
Weight per piece (including packing)	16.5 g
Weight per piece (excluding packing)	15 g
Customs tariff number	85235190
Country of origin	DE

CF FLASH 256MB APPLIC A - Memory



2988793

<https://www.phoenixcontact.com/us/products/2988793>

Technical data

Product properties

Product type	Storage medium
Application	License key for applications
Memory type	FLASH-EPROM
Memory size	256 Mbyte

Electrical properties

Maximum power dissipation for nominal condition	0.4 W
---	-------

Supply

Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC
Typical current consumption	typ. 120 mA

Dimensions

Width	36.4 mm
Height	42.8 mm
Depth	3.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

CF FLASH 256MB APPLIC A - Memory



2988793

<https://www.phoenixcontact.com/us/products/2988793>

Classifications

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

CF FLASH 256MB APPLIC A - Memory



2988793

<https://www.phoenixcontact.com/us/products/2988793>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com