

SD FLASH 256MB APPLIC A - Program/configuration memory



2988816

<https://www.phoenixcontact.com/us/products/2988816>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 256 MB with license key for function block libraries. For licensed function blocks, please refer to the documentation.

Similar figure

Product description

Program and configuration memory for storing the application program and other files in the file system of the PLC, with customer-specific licence bits and license key for function block libraries. For licensed function block libraries, please refer to the documentation.

Individual function blocks from Phoenix Contact are licensed, which means that a fee is charged for each controller on which licensed blocks are to be used. The blocks check the license stored on the controller during runtime and enable themselves or run for a limited time in demo mode. For the licensed function block libraries, please refer to the documentation

Please observe the specified performance data of your controller(s) and check that it/they are suitable for your application.

For users who do not use the function block libraries, the program and configuration memory is also available without a license as an option.

Your advantages

- Program and configuration memory, plug-in, with license key for function block libraries
- For storing application programs and other files in the file system of the PLC

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2988816 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR10 |
| Product key | DRAAZA |
| GTIN | 4046356447126 |
| Weight per piece (including packing) | 9.2 g |
| Weight per piece (excluding packing) | 8.5 g |
| Customs tariff number | 85235199 |
| Country of origin | DE |

SD FLASH 256MB APPLIC A - Program/configuration memory



2988816

<https://www.phoenixcontact.com/us/products/2988816>

Technical data

Product properties

| | |
|-------------------|------------------------------|
| Product type | Storage medium |
| Application | License key for applications |
| Mounting position | vertical |
| Memory type | FLASH-EPROM |
| Memory size | 256 Mbyte |

Electrical properties

| | |
|-------------------------------------------------|---------|
| Maximum power dissipation for nominal condition | 0.165 W |
|-------------------------------------------------|---------|

Supply

| | |
|-----------------------------|-----------------------|
| Supply voltage | 3.3 V DC |
| Supply voltage range | 2.7 V DC ... 3.6 V DC |
| Typical current consumption | typ. 50 mA |

Material specifications

| | |
|------------------|---------|
| Housing material | Plastic |
|------------------|---------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
|---------------------------------|------------------|

Mounting

| | |
|-------------------|----------|
| Mounting position | vertical |
|-------------------|----------|

SD FLASH 256MB APPLIC A - Program/configuration memory



2988816

<https://www.phoenixcontact.com/us/products/2988816>

Environmental product compliance

China RoHS

| | |
|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com