

# FBRN 10-4 N - Fixed bridge



3001624

<https://www.phoenixcontact.com/us/products/3001624>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fixed bridge, pitch: 4.2 mm, number of positions: 10, color: silver-colored



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3001624       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE19          |
| Product key                          | BE1Z2X        |
| GTIN                                 | 4017918107192 |
| Weight per piece (including packing) | 3.97 g        |
| Weight per piece (excluding packing) | 3.89 g        |
| Customs tariff number                | 85369095      |
| Country of origin                    | PL            |

# FBRN 10-4 N - Fixed bridge



3001624

<https://www.phoenixcontact.com/us/products/3001624>

## Technical data

### Product properties

|                     |              |
|---------------------|--------------|
| Product type        | Screw bridge |
| Number of positions | 10           |
| Pitch               | 4.2 mm       |

### Dimensions

|       |        |
|-------|--------|
| Pitch | 4.2 mm |
|-------|--------|

### Material specifications

|                     |                |
|---------------------|----------------|
| Color               | silver-colored |
| Material            | Cu             |
| Insulating material | PA             |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

# FBRN 10-4 N - Fixed bridge



3001624

<https://www.phoenixcontact.com/us/products/3001624>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# FBRN 10-4 N - Fixed bridge



3001624

<https://www.phoenixcontact.com/us/products/3001624>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.056 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)