


# EB 36-27/L1-L2-L3 - Insertion bridge



3009354

<https://www.phoenixcontact.com/us/products/3009354>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, pitch: 27 mm, number of positions: 36, color: gray

## Commercial data

Item number	3009354
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918091804
Weight per piece (including packing)	625 g
Weight per piece (excluding packing)	625 g
Customs tariff number	85366990
Country of origin	DE

# EB 36-27/L1-L2-L3 - Insertion bridge



3009354

<https://www.phoenixcontact.com/us/products/3009354>

## Technical data

### Product properties

Product type	Insertion bridge
Number of positions	36
Pitch	27 mm

### Dimensions

Pitch	27 mm
-------	-------

### Material specifications

Color	gray (RAL 7042)
Material	Copper
Insulating material	PA

### Mounting

Mounting type	Screw mounting
---------------	----------------

# EB 36-27/L1-L2-L3 - Insertion bridge



3009354

<https://www.phoenixcontact.com/us/products/3009354>

## Classifications

### ECLASS

ECLASS-13.0

27250303

### ETIM

ETIM 9.0

EC000489

### UNSPSC

UNSPSC 21.0

39121400

# EB 36-27/L1-L2-L3 - Insertion bridge



3009354

<https://www.phoenixcontact.com/us/products/3009354>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)