# FBSL 4-8 - Plug-in bridge

3030326

https://www.phoenixcontact.com/us/products/3030326

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in bridge, pitch: 8.2 mm, number of positions: 4, nominal current: 41 A, color: red

## Your advantages

- The 2- to 50-pos. jumpers can bridge up to 50 terminal blocks in the two bridge shafts of the CLIPLINE complete system in one step

## Commercial data

| | |
|---|---|
| Item number | 3030326 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z2X |
| GTIN | 4055626029160 |
| Weight per piece (including packing) | 5.31 g |
| Weight per piece (excluding packing) | 5.229 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Plug-in bridge |
| Number of positions | 4 |
| Pitch | 8.2 mm |

### Electrical properties

| | |
|---|---|
| Maximum load current | 41 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |

### Connection data

| | |
|---|---|
| Maximum load current | 41 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |

### Dimensions

| | |
|---|---|
| Width | 31.1 mm |
| Height | 20.38 mm |
| Depth | 20.38 mm |
| Pitch | 8.2 mm |

### Material specifications


| | |
|---|---|
| Color | red (RAL 3001) |
| Material | Copper |
| Flammability rating according to UL 94 | V0 |
| Insulating material | PA |

### Mounting

| | |
|---|---|
| Mounting type | Plug-in mounting |

## Drawings

Schematic diagram



## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000489 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.053 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com