

DP PS-3,5 - Spacer plate



3031011

<https://www.phoenixcontact.com/us/products/3031011>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer plate, depth: 33.5 mm, width: 3.5 mm, height: 15.9 mm, number of positions: 1, color: red



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3031011 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z3X |
| GTIN | 4046356728010 |
| Weight per piece (including packing) | 0.84 g |
| Weight per piece (excluding packing) | 0.83 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

DP PS-3,5 - Spacer plate



3031011

<https://www.phoenixcontact.com/us/products/3031011>

Technical data

Product properties

| | |
|---------------------|-----------------|
| Product type | Partition plate |
| Number of positions | 1 |

Material specifications

| | |
|--|----------------|
| Color | red (RAL 3001) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|--------|---------|
| Width | 3.5 mm |
| Height | 15.9 mm |
| Depth | 33.5 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

DP PS-3,5 - Spacer plate



3031011

<https://www.phoenixcontact.com/us/products/3031011>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

DP PS-3,5 - Spacer plate



3031011

<https://www.phoenixcontact.com/us/products/3031011>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.02 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com