

UAB 1 - Support bracket

3032431

<https://www.phoenixcontact.com/us/products/3032431>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Support bracket, number of positions: 1, mounting type: DIN rail mounting, color: gray



Commercial data

Item number	3032431
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1ZWX
GTIN	4017918092269
Weight per piece (including packing)	6.017 g
Weight per piece (excluding packing)	6 g
Customs tariff number	39269097
Country of origin	DE

UAB 1 - Support bracket



3032431

<https://www.phoenixcontact.com/us/products/3032431>

Technical data

Product properties

Product type	Support bracket
Number of positions	1
Pitch	200 mm

Dimensions

Width	2 mm
Height	74.3 mm
Depth on NS 32	47 mm
Pitch	200 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UAB 1 - Support bracket

3032431

<https://www.phoenixcontact.com/us/products/3032431>



Classifications

ECLASS

ECLASS-13.0	27400607
ECLASS-15.0	27400607

ETIM

ETIM 10.0	EC001166
-----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

UAB 1 - Support bracket



3032431

<https://www.phoenixcontact.com/us/products/3032431>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.022 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com